

Comfort / Titan Series Fluid Warmers



Safety is a priority with Entthermics Series fluid warmers. Ensure fluids are safely warmed to recommended temperatures through the WarmSafe™ zone heating system. WarmRight® technology provides the right temperature for the right product to meet healthcare guidelines for IV and irrigation fluids.

The patient-friendly Comfort Series allows you to put aesthetically pleasing warming units right where they are needed, allowing nurses and aides to maximize their time.

The durable Titan Series provides years of worry-free service.

The lighting inside the warmers softens the patient's room, placing more emphasis on comfort and care.

WarmSafe Zone Heating: Heat is evenly balanced throughout the chamber to provide safe fluid warming.

Convenient: Keep in patient or procedure rooms with this countertop model.

Service: Our worldwide support team is dedicated to providing quality equipment. We walk with you every step of the way to maximize your return on investment.

Glass Door: Energy-efficient coated glass door reflects heat back into the cavity.

Mobile: Optional casters or mobile cart

Made in the USA with a commitment to quality

Warranty: 5-year parts/1-year labor (US/Canada only)

An ISO 13485:2016 certified company

Standard Features

- Windowed door
- Organizational basket
- Epoxy-coated interior surfaces
- Programmable control with temperature lock feature
- Interior lighting with a comforting blue glow
- Temperature management access point
- Four (4) non-skid rubber feet



CAPACITY

- 16** 2.5 ft³ (DC250L/EC250L)
16 (1) Liter bags or 12 x (1) liter bottles
- 24** 3.5 ft³ (EC350L -Titan Series only)
24 (1) Liter bags or bottles
- 28** 4.0 ft³ (DC400L/EC400L)
28 (1) Liter bags or 20 (1) liter bottles



TEMPERATURE

- Adjustable temperature range of
- 32°-40°C (90°-104°F) adjustable injection mode
- 32°-66°C (90°-150°F) adjustable irrigation mode
- Accurate temperature
- IRR +0/-1.67°C (-3°F)
- INJ +0/-1.10°C (-2°F)

Comfort Series



DC250L



DC400L

Titan Series



EC250L



EC350L



EC400L

Configurations (select one)

Series

- ☐ Comfort (DC) ☐ Titan (EC)

Size

- ☐ 2.5 ft³ ☐ 3.5 ft³ (Titan Series only) ☐ 4.0 ft³

Door Assembly

- ☐ Windowed door (standard) ☐ Solid door (Titan Series only)

Door Swing

- ☐ Right hinged (standard) ☐ Left hinged

Door lock

- ☐ No lock (standard) ☐ Manual lock

Baskets - Comfort Series

- ☐ 2 baskets (standard) ☐ 1 basket

Baskets - Titan Series

- ☐ 1 basket (standard-EC250L & EC400L)
- ☐ 2 baskets (EC250L & EC400L)
- ☐ 1 basket and 1 shelf (standard-EC350L)

Data logger - WarmWatch® (historical temperature record) - not available on EC/DC400L

- ☐ No data logger (standard) ☐ Data logger

Electrical

- ☐ 120V 1PH ☐ 220V 1PH ☐ 230V 1PH

Accessories (select all that apply)

Bumper and Caster Assembly 3" (76mm) casters, 2 rigid; 2 swivel with Brake; overall height increases by 5" (127mm)

- ☐ DC250L (5017546)
- ☐ DC400L (5017547)
- ☐ EC250L or EC350L (5017548)
- ☐ EC400L (5017549)

Caster Package with Plate 3" (76mm) casters, 2 rigid; 2 with Brake; overall height increases by 5" (127mm)

- ☐ DC250L (5017542)
- ☐ DC400L (5017543)
- ☐ EC250L or EC350L (5017544)
- ☐ EC400L (5017545)

Cart, Mobile

- ☐ 3.5" (89mm) casters, 2 swivel; 2 swivel with brake (5024661);
36.5" (876mm) H x 26" (660mm) W x 26" (660mm) D

Anchorage (4 required)

- ☐ Anti-tip bracket (1014403)


Goldfish Label

- ☐ Goldfish Label (LA-46988)


Stacking Kits

It is recommended that fluid warming units be placed at or near the bottom of the stacked configuration whenever possible for maximum stability - not available with casters


- ☐ DC250L double-stacked or under DC250 or DC350 (5013021)
- ☐ DC400L double-stacked (5013024)
- ☐ EC250L or EC350L double-stacked or under EC250 or EC350 (5017272)
- ☐ EC400L double-stacked (5017273)



EC/DC250L



EC/DC400L



Comfort/Titan Series Fluid Warmers



Specification



Top: 1"
Left: 1"
Right: 1"
Back: 3"

CLEARANCE



DIMENSIONS

Model	Exterior (H x W x D)	Interior (H x W x D)	Net Weight
DC250L	22"(559mm) x 18.5"(470mm) x 22.0"(559mm)	15.25"(387mm) x 15.5"(394mm) x 18.75"(476mm)	67 lbs (30 kg)
EC250L	22"(559mm) x 18.5"(470mm) x 23.5"(597mm)	15.25"(387mm) x 15.5"(394mm) x 18.75"(476mm)	67 lbs (30 kg)
EC350L	28"(711mm) x 18.5"(470mm) x 23.5"(597mm)	21.25"(540mm) x 15.5"(394mm) x 18.75"(476 mm)	91 lbs (41 kg)
DC400L	22"(559mm) x 24.0"(610mm) x 24.3"(617mm)	15.25"(387mm) x 21.0"(533mm) x 21.75"(552 mm)	100 lbs (45 kg)
EC400L	22"(559mm) x 24.0"(610mm) x 25.75"(654mm)	15.25"(387mm) x 21.0"(533mm) x 21.75"(552 mm)	100 lbs (45 kg)

	Ship Dimensions (L x W x H)*	Ship Weight*
EC/DC250L	35" x 23" x 30"	116 lbs
EC350L	35" x 23" x 42"	144 lbs
EC/DC400L	31" x 31" x 32"	158 lbs

*Domestic ground shipping information. Contact factory for export weight and dimensions.



ELECTRIC

	V	Ph	Hz	A	kW	Plug Configuration
EC/DC250L	120	1	60	3.7	0.44	NEMA 5-15P; 15A 125V Plug; Hospital Grade
	220	1	60	2.0	0.44	CEE 7/7 220-230V Plug
	230	1	50/60	1.9	0.44	BS 1363 Plug; CEE 7/7 220-230V Plug
EC350L	120	1	60	3.7	0.44	NEMA 5-15P; 15A 125V Plug; Hospital Grade
	220	1	50	2.0	0.44	CEE 7/7 220-230V Plug
	230	1	50/60	1.9	0.44	BS 1363 Plug; CEE 7/7 220-230V Plug
EC/DC400L	120	1	60	5.8	0.7	NEMA 5-15P; 15A 125V Plug; Hospital Grade
	220	1	50	3.1	0.7	CEE 7/7 220-230V Plug
	230	1	50/60	3.0	0.7	BS 1363 Plug; CEE 7/7 220-230V Plug



IPX-0

*Other international plugs are available, contact the manufacturer for more information.

**Electrical connections must meet all applicable federal, state and local codes.

CONTACT US

W164 N9221 Water Street | Menomonee Falls, Wisconsin 53051 | U.S.A.
Phone: 262.251.8356 | 800.862.9276 | Fax: 262.251.7067 | enthermics.com